



Desiccator, Non-vacuum

Proizvod #:	1428500
EUR Cijena:	Kontaktirajte nas
Nije prikazan datum isporuke	

Round polycarbonate cover and polypropylene base. Non-Vacuum. Chamber is impervious to alkali and acidic conditions. Recessed rim prevents grease (not included) from contacting bench surfaces when removed and eliminates need for a separate gasket. Dimensions (height x diam): 245 mm x 330 mm (9.7" x 13"). Holds 454 g (1 lb) of dessicant. Ceramic dessicator plate (sold separately) is inert, non-stick, and corrosion resistant. Quadrants crafted into plate for easy tracking of material locations. Plate diameter: 230 mm (9").

Specifikacije

Volument/ veličina paketa:	1 each
----------------------------	--------