



Desiccator cabinet, non-vacuum

Proizvod #:	2618100
EUR Cijena:	Kontaktirajte nas
Nije prikazan datum isporuke	

Stackable, polystyrene, transparent from any side. Door has foam rubber gasket, two roller latches for airtight fit. Inside dimensions: 21 x 18 x 13 cm (8.25 x 7 x 5"). Door opening: 19 x 11 cm (7.5 x 4.4"). Desiccator Grease and silica gel available and sold separately.

Specifikacije

Volumen/ veličina paketa:	1 each
---------------------------	--------