



Digital extension cable for SC sensors, 30 m

Proizvod #: LZX852
EUR Cijena: Kontaktirajte nas
Nije prikazan datum isporuke

Specifikacije

Duljina kabla:	30 m
Izolacijski otpor:	$\geq 20 \text{ M}\Omega \times \text{km}$ at 20 °C
Kodiranje žica:	AWG 22: brown (+12 V DC) Black (circuit common) AWG 26: white (data -) blue (data +)
Materijal:	Cable: Cu: AWG 22 - 19×0.15 mm AWG 26 - 18×0.10 mm
Minimal bend radius:	7.5 × outer diameter, flexible installation
Minimal bend radius 2:	5 × outer diameter, fixed installation
Normalna voltaža:	250 V Vpp
Otpor vala:	ca. 95 Ω at 1 kHz, AWG 22 pairs
Otpornost žica:	max. 106 Ω/km AWG 22 at 20 °C (loop)
Outside coat:	PUR (Elastoplan 1185), RoHS-conformal
Promjer, vanjski:	6.8 mm $\pm$ 0.3 mm
Radna temperatura:	- 80 °C Fixed Installation
Shield attenuation:	$\geq 55 \text{ dB}$
Testna voltaža:	1200 V Vrms
	wire/wire

Ukupna zaštita:

Cu- netting, tinned