



Džepni kolorimetar POCKET Colorimeter II Kolorimetar za 420 nm

Proizvod #:

5870042

NEDOSTUPAN ARTIKL

Ovaj artikl više nije dostupan.

Analiza mala veličinom, ali velike vodootpornosti

Čvrsti i pouzdani fotometar s filterom određene valne duljine. Korisnik može programirati. U kovčegu, zajedno s reagensima, kivetama i uputama za korištenje.

Generic POCKET Colorimeter II Instruments are intended for applications not included in standard analysis systems. They are available in a range of wavelengths appropriate for many custom calibrations. In addition to the factory absorbance calibration (0-2.5 A), the instruments offer two user-entered, two-point, linear calibrations, and provide a choice of either 0.00 to 2.55 or 0.0 to 99.0 for the display value.

Jednostavno: sve su funkcije dostupne pomoću samo četiri tipke

Napajanje: rad na bateriji za maksimalno 2000 testova

Jasna očitavanja čak i u teškim uvjetima, zahvaljujući osvjetljenju i velikim znamenkama na zaslonu

Pouzdana rezultati i bez uključivanja u napajanje

Čvrsta konstrukcija, ali mala težina

Specifikacije

Broj testova:	Up to 18
Detektor:	Detektor silicija
Dimenzije (V x Š x D):	35 mm x 61 mm x 155 mm
Duljina puta kivete:	25 mm ili 1 cm s adapterom
Garancija:	24 mjeseci
Klasa kućišta:	IP67
Lamp Type:	Svjetleća dioda (LED)
Masa:	0,23 kg
Parametar:	Wavelength specific, 420 nm
Potvrde o sukladnosti:	European CE mark
Preciznost valne duljine:	Fiksna valna duljina ± 2 nm razlikuje se među modelima
Što je u pretincu:	Each wavelength specific Pocket Colorimeter II Instrument comes complete as a ready-to-use kit in a sturdy custom carrying case, including a printed manual.
Valna duljina:	Fixed wavelength ± 2 nm varies with model

Zaslon: LCD, pozadinsko osvjetljenje

Što je u pretincu

Each wavelength specific Pocket Colorimeter II Instrument comes complete as a ready-to-use kit in a sturdy custom carrying case, including a printed manual.