



pH electrode with TOP68 connector

Proizvod #: LZX540
EUR Cijena: Kontaktirajte nas
Nije prikazan datum isporuke

High-pH-glass and single reference system, electrode for waster with high pH levels

Specifikacije

Dijafragma:	Ring diaphragm, porous PTFE
Dubina uranjanja:	120 mm
Duljina:	140 mm
Garancija:	6 mjeseci
Materijal:	Sensor: Glass
Mjerni rang:	0 - 80 °C
Navoj senzora:	Pg 13,5
Promjer:	12 mm
Rang tlaka:	3,5 bar
Referentna elektroda:	Gel KCl/AgCl
Spajanje kabla:	TOP68 connector
Temperaturni senzor:	Pt100 integrated